



Powering Business Worldwide

pe.eaton.com

Midsize AC Rated Rocker

250411E

UPC:782116550586

Dimensions:

- **Height:** .982 IN
- **Length:** 1.248 IN
- **Width:** 1.029 IN

Warranties:

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warrantied for one (1) year from the date of shipment.

Specifications:

- **Amperage Rating:** 15A at 125 Vac, 10A at 250 Vac, 10A at 28 Vdc, 8A at 14VT, ENEC: 10(2)A at 250V
- **Circuit Number:** 14
- **Circuit Position Center:** OFF
- **Circuit Position Down:** ON
- **Frame Color:** Black
- **Number Of Poles:** Two-pole
- **Terminals:** 0.250-inch spade terminal
- **Throw Type:** Double-throw

Supporting documents:

- [Eatons Volume 11-Vehicle and Commercial Controls](#)
- [Eaton Specification Sheet - 250411E](#)

Certifications:

- UL Recognized
- CSA Certified

Product compliance:

- ENEC Marked
- RoHS Compliant



