



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Type C361 Flange Mounted Disconnect Switch

**C361NC**

**UPC:**782113566504

### Dimensions:

- **Height:** 8.5 IN
- **Length:** 12.1 IN
- **Width:** 10.3 IN

**Notes:**Maximum horsepower ratings refer to switch only. DOES NOT include handle, must be purchased separately.

### Warranties:

- 1 year

### Specifications:

- **Type:** Switch and operating mechanism only
- **Amperage Rating:** 30A
- **Depth Range:** 7-16 in
- **Fuse Clip Rating:** Non-fusible
- **Max Hp Rating:** 7.5 hp at 208 Vac, 7.5 hp at 240 Vac, 15 hp at 480 Vac, 20 hp at 600 Vac, 5 hp at 250 Vdc
- **Mounting:** Right-hand
- **Wire Size:** #2-14 AWG Cu/Al

### Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - C361NC](#)

### Certifications:

- CSA Certified
- UL Listed

**Product compliance:** No Data

