



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## DOE 2016 Efficient Transformer, Dry-type, Ventilated, Three- phase

CV29M47T4516

UPC:786680206535

### Dimensions:

- **Height:** 36.88 IN
- **Length:** 21.13 IN
- **Width:** 24.88 IN

**Weight:**1.1 LB

**Notes:**10 CFR Part 431 (2016) Efficient

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Coil Material:** Aluminum
- **Efficiency:** DOE2016
- **Enclosure:** NEMA 2
- **Frame:** 940
- **Frequency Rating:** 60 Hz
- **Insulation:** 220C
- **Kva Rating:** 45 kVA
- **Phase:** Three-phase
- **Primary Voltage:** 208 DELTA
- **Secondary Voltage:** 480Y/277
- **Sound Level:** NEMA ST-20
- **Tap Size:** 2 at +2.5%, 4 at -2.5%
- **Temperature Rating:** 150°C rise
- **Voltage Rating:** 208
- **Weathershield:** WS58
- **Wiring Connection:** E0352B

**Supporting documents:**



- [Eaton Specification Sheet - CV29M47T4516](#)

**Certifications:**

- UL Listed
- CSA Certified

**Product compliance:**

- DOE2016 Efficient

---

© 2016 Eaton. All rights reserved.