



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Heavy Duty Hesitation Switches

7991K10

UPC:786685677477

### Dimensions:

- **Height:** .97 IN
- **Length:** 1.45 IN
- **Width:** 1.32 IN

### Warranties:

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warrantied for one (1) year from the date of shipment.

### Specifications:

- **Type:** Bat lever
- **Amperage Rating:** 15A at 125V, 10A at 250V
- **Bushing Length:** 0.469 in
- **Circuit Number:** F
- **Circuit Position Center:** OFF
- **Circuit Position Down:** ON
- **Horsepower:** 0.75 hp at 250V
- **Lever Length:** 0.688 in
- **Number Of Poles:** Three-pole
- **Terminals:** Screw terminal
- **Throw Type:** Double-throw

### Supporting documents:

- [Eatons Volume 11-Vehicle and Commercial Controls](#)
- [Eaton Specification Sheet - 7991K10](#)

### Certifications:

- CSA Certified
- UL Recognized

**Product compliance:** No Data



