



Powering Business Worldwide

pe.eaton.com

Series G, JG-frame Molded Case Circuit Breaker

JGS9250AAG

UPC:782114889251

Dimensions:

- **Height:** 7 IN
- **Length:** 3.57 IN
- **Width:** 5.34 IN

Weight:8 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Complete breaker
- **Amperage Rating:** 250A
- **Interrupt Rating:** 85 kAIC at 240V, 40 kAIC at 415V, 35 kAIC at 480V, 18 kAIC at 600V
- **Number Of Poles:** Four-pole
- **Voltage Rating:** 600V
- **Mounting Hardware:** Metric
- **Frame Size:** JG-frame
- **Series:** Series G
- **Terminals:** Line and load
- **Trip Type:** Adjustable thermal, adjustable magnetic

Supporting documents:

- [Eatons Volume 4-Circuit Protection](#)
- [Installation Instructions for Series G J-Frame Circuit Breakers](#)
- [J-Frame 310+ and L-Frame 310+ Molded-case circuit breakers](#)
- [Eaton Specification Sheet - JGS9250AAG](#)



Certifications:

- CSA Certified
- UL Listed
- IEC Rated

Product compliance:

- CE Marked

© 2016 Eaton. All rights reserved.