



Powering Business Worldwide

pe.eaton.com

22.5 mm, Non-metallic, Selector Switch Operator

E22VBF1

UPC:782113469737

Dimensions:

- **Height:** .5 IN
- **Length:** 1.5 IN
- **Width:** 1.5 IN

Weight:.1 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** 22.5 mm, Non-metallic Heavy-Duty
- **Actuator:** Lever
- **Actuator Color:** Black
- **Cam Code:** Cam 2
- **Enclosure:** NEMA 3, 3R, 4, 4X, 12, 13
- **Illumination:** Non-illuminated
- **Number Of Positions:** Two-position
- **Series:** E22
- **Throw Type:** 45° Throw

Supporting documents:

- [Eatons Volume 12-Aftermarket, Renewal Parts and Life Extension Solutions](#)
- [Pushbuttons, Indicating lights, Selector switches and Stacklights](#)
- [Eaton Specification Sheet - E22VBF1](#)

Certifications:

- IEC 947-5-1 MTTA
- CSA Certified
- UL 508



- Lloyd's Register Certified

Product compliance:

- CE Marked

© 2016 Eaton. All rights reserved.