



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## 22.5 mm, Non-metallic, Selector Switch Operator

**E22WG3**

**UPC:**782113487519

### Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

**Notes:** Will accept a maximum of 2 contact blocks (4 circuits) with supplied 3-way mounting adapter. Optional 5-way adapter will accept a maximum of 4 contact blocks (8 circuits). Includes lamp extender.

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** 22.5 mm, Non-metallic Heavy-Duty
- **Actuator:** Lever
- **Actuator Color:** Green
- **Bezel:** Chrome
- **Cam Code:** Cam 1
- **Enclosure:** NEMA 3, 3R, 4, 4X, 12, 13
- **Illumination:** Illuminated
- **Number Of Positions:** Three-position
- **Series:** E22
- **Throw Type:** 45° Throw

### Supporting documents:

- [Pushbuttons, Indicating lights, Selector switches and Stacklights](#)
- [Eaton Specification Sheet - E22WG3](#)

### Certifications:

- CSA Certified



- IEC 947-5-1 MTTA
- UL 508
- Lloyd's Register Certified

**Product compliance:**

- CE Marked

---

© 2016 Eaton. All rights reserved.