



Powering Business Worldwide

pe.eaton.com

E50 Heavy Duty Factory Sealed 6P+ Limit Switch

E50ANR16P

UPC:782113131405

Dimensions:

- **Height:** 4.67 IN
- **Length:** 1.54 IN
- **Width:** 2.25 IN

Weight:2.1 LB

Notes:CW (clockwise) and CCW (counterclockwise) operation; easily convertible to CW only or CCW only operation

Warranties:

- 1 year

Specifications:

- **Accuracy:** Refer to installation publication P15836
- **Connection:** 8 Ft. (2.5m) Cable
- **Contact Rating:** 10A at 240Vac, 1A at 125Vdc
- **Cable Type:** SOOW-A
- **Contact Configuration:** 1NO-1NC
- **Cord Length:** 96 FT
- **Enclosure Material:** Die Cast Zinc
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67, IP69K
- **Led Indicators:** Neon (120 Vac)
- **Maximum Ac Current:** 10A
- **Maximum Dc Current:** 1A
- **Operating Temperature:** 10° to 201°F (-12° to 94°C)
- **Switch Type:** Side Rotary

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50ANR16P](#)



Certifications:

- CSA Certified
- UL Listed

Product compliance:

- CE Marked

© 2016 Eaton. All rights reserved.