



Powering Business Worldwide

pe.eaton.com

E50 Heavy Duty Plug-In Limit Switch

E50SGN

UPC:782113308791

Dimensions:

- **Height:** 3.13 IN
- **Length:** 1.54 IN
- **Width:** 1.78 IN

Weight:.3313 LB

Warranties:

- 1 year

Specifications:

- **Contact Rating:** 5A at 120 Vac
- **Contact Configuration:** 1NO-1NC
- **Enclosure Material:** Die Cast Zinc
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67
- **Led Indicators:** Neon (120 Vac)
- **Maximum Ac Current:** 5A
- **Operating Temperature:** 14° to 201°F (-10° to 94°C)

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50SGN](#)

Certifications: No Data

Product compliance: No Data

