



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## E51 Series, Limit Switch Style, Modular Inductive Photoelectric Sensor

**E51CLC1**

**UPC:**782113213866

### Dimensions:

- **Height:** 4.89 IN
- **Length:** 1.54 IN
- **Width:** 1.82 IN

**Weight:**.975 LB

### Warranties:

- 3 year

### Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 1.0A Solid State Output
- **Contact Configuration:** L1 Switched, N.O. and N.C.
- **Enclosure Material:** Receptacle and Body: Die Cast Zinc, Head: Plastic
- **Environmental Rating:** NEMA 3,3S,4,4X,6,6P,12,13, IP67
- **Input Voltage:** 120 Vac
- **Led Indicators:** Red Output Status for both outputs
- **Maximum Ac Current:** 1.0A
- **Operating Mode:** Thru-Beam
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Sensor Type:** Through Beam
- **Switch Type:** Photoelectric

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E51CLC1](#)

### Certifications:



- UL Listed
- CSA Certified

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.