



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Photoelectric Sensor

**E51CLP1**

**UPC:**782113146935

### Dimensions:

- **Height:** 1.89 IN
- **Length:** 4.99 IN
- **Width:** 1.54 IN

### Warranties:

- 3 year

### Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 1.0A solid state output
- **Contact Configuration:** L1 switched
- **Enclosure Material:** Die cast zinc
- **Environmental Rating:** NEMA 3, 3S, 4, 4X, 6, 6P, 12, 13, IP67
- **Input Voltage:** 120V
- **Led Indicators:** Output ON (1 LED per output)
- **Maximum Ac Current:** 1.0A
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Sensor Type:** Retroreflective
- **Series:** E51

### Supporting documents:

- [Eaton's Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E51CLP1](#)

### Certifications:

- UL Listed
- CSA Certified

**Product compliance:** No Data

