



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## E51 Series, Limit Switch Style, Modular Inductive Photoelectric Sensor Head

**E51DF3**

**UPC:**782113478258

### Dimensions:

- **Height:** 1.77 IN
- **Length:** 1.54 IN
- **Width:** 1.82 IN

**Weight:**.1625 LB

**Notes:**Glass Fiber Optic cables not included. Will not work with E51RA Receptacle &E51SAL Body.

### Warranties:

- 3 year

### Specifications:

- **Enclosure Material:** Plastic
- **Environmental Rating:** NEMA 3,3S,4,4X,6,6P,12,13, IP67
- **Operating Mode:** Fiberoptic
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Switch Type:** Photoelectric

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E51DF3](#)

### Certifications:

- UL Listed
- CSA Certified

### Product compliance:

- CE Marked



