



Powering Business Worldwide

pe.eaton.com

E51 Series, Limit Switch Style, Modular Inductive Photoelectric Sensor Head

E51DP22

UPC:782113148823

Dimensions:

- **Height:** 1.77 IN
- **Length:** 1.54 IN
- **Width:** 1.82 IN

Weight:.1625 LB

Notes: Heads feature a light or dark operation selector switch which reverses the output function. Have mechanical Near/Far adjustment for optimum performance. Adjustments need to be made before mounted on the body

Warranties:

- 3 year

Specifications:

- **Enclosure Material:** Plastic
- **Environmental Rating:** NEMA 3,3S,4,4X,6,6P,12,13, IP67
- **Operating Mode:** Diffuse Reflective
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Switch Type:** Photoelectric

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E51DP22](#)

Certifications:

- CSA Certified
- UL Listed

Product compliance:

- CE Marked



