



Powering Business Worldwide

pe.eaton.com

E58 Series Tubular Plastic Body Photoelectric Sensor

E58CAL18T110D2

UPC:782113109657

Dimensions:

- **Height:** 2.2 IN
- **Length:** .47 IN
- **Width:** .71 IN

Weight:.2875 LB

Notes:Short circuit and reverse polarity protected

Warranties:

- 3 year

Specifications:

- **Connection:** 9.8 Ft. (3m) Cable
- **Contact Rating:** NPN: 250 mA at 30Vdc
- **Cable Type:** PVC
- **Contact Configuration:** NPN Open Collector
- **Cord Length:** 120 FT
- **Diameter:** .71 IN
- **Enclosure Material:** Stainless Steel
- **Environmental Rating:** NEMA 1, 3, 4, 4X, 6, 12 and 13, IP69k
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Red Output Status
- **Maximum Dc Current:** 250 mA
- **Operating Mode:** Diffuse Reflective
- **Operating Temperature:** -40° to 158°F (-40° to 70°C)
- **Protection:** Auto reset short circuit
- **Switch Type:** Photoelectric

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E58CAL18T110D2](#)



Certifications: No Data

Product compliance: No Data

© 2016 Eaton. All rights reserved.