



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## General-Purpose Encapsulated Transformer

**Y38M19T30A**

**UPC:**786680010163

### Dimensions:

- **Height:** 17.38 IN
- **Length:** 10.52 IN
- **Width:** 20 IN

**Weight:**422 LB

**Notes:**Model A

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** General-Purpose Encapsulated Transformer
- **Design:** EPT
- **Coil Material:** Aluminum windings
- **Enclosure:** NEMA 3R
- **Frame:** 243
- **Frequency Rating:** 60 Hz
- **Phase:** Three-phase
- **Primary Voltage:** 380V
- **Secondary Voltage:** 190Y/110V
- **Tap Size:** 2 at +2.5% FCAN, 4 at -2.5% FCBN
- **Temperature Rating:** 115°C
- **Volt Ampere Rating:** 30 KVA
- **Weathershield:** Indoor-Outdoor
- **Wiring Connection:** 84AC

### Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - Y38M19T30A](#)



**Certifications:**

- UL Listed

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.