



Powering Business Worldwide

pe.eaton.com

NEMA Freedom Line Enclosed Control

ECN1601ABC

UPC:782114029497

Dimensions:

- **Height:** 7 IN
- **Length:** 27 IN
- **Width:** 11 IN

Weight:25 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Coil Voltage:** 110V/50 Hz or 120V/60 Hz
- **Enclosure:** NEMA 1
- **Type:** Combination non-reversing starter
- **Actuator:** START/STOP pushbutton
- **Disconnect Current Rating:** 30A/600V
- **Disconnect Fuse Clip Type:** Type R
- **Number Of Poles:** Three-pole
- **Starter Size:** NEMA size 0

Supporting documents:

- [Eatons Volume 10-Enclosed Control](#)
- [Eaton Specification Sheet - ECN1601ABC](#)

Certifications:

- UL Listed file E1491

Product compliance: No Data

