



Powering Business Worldwide

pe.eaton.com

Molded Case Engine Generator Circuit Breaker

KG3400S46

UPC:786679076606

Dimensions:

- **Height:** 6.2 IN
- **Length:** 12.3 IN
- **Width:** 6.9 IN

Weight:10 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Amperage Rating:** 400A
- **Number Of Poles:** Three-pole
- **Feed Type:** Reverse
- **Frame:** KG-frame
- **Generator Rating:** 144 kVA/116 kW at 240V, 289 kVA/231 kW at 480V, 361 kVA/289 kW at 600V
- **Pickup:** 1000-2000
- **Series:** Series C
- **Shunt Trip:** 12-24 Vac/dc right pigtail rear
- **Terminals:** Line and load
- **Trip Type:** Thermal magnetic

Supporting documents:

- [Eaton's Volume 4-Circuit Protection](#)
- [Series C Engine Generator Circuit Breakers - Dimension Sheets](#)
- [Eaton Specification Sheet - KG3400S46](#)

Certifications:

- CSA Std. C22.2 No. 5



- CSA Certified
- UL Listed
- IEC 947-2
- UL 489
- IEC Rated

Product compliance: No Data

© 2016 Eaton. All rights reserved.