



Powering Business Worldwide

pe.eaton.com

Eaton's Solar Power Center Meter Breaker

CMBE4242PV200TS

UPC:786685690162

Dimensions:

- **Height:** 34.17 IN
- **Length:** 5.31 IN
- **Width:** 22.52 IN

Weight:45 LB

Warranties:

- Limited lifetime

Specifications:

- **Special Features:** Side by side construction
- **Type:** CH solar-ready
- **Amperage Rating:** 200A
- **Bus Material:** Copper
- **Bus Rating:** 225 A
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Galvanized steel
- **Feed Type:** Overhead
- **Input:** 70 max PV input
- **Interrupt Rating:** 22 kAIC
- **Main Circuit Breaker:** CSR
- **Mounting:** Surface mounting
- **Number Of Circuits:** 42
- **Number Of Sockets:** 1
- **Phase:** Single-phase
- **Used With:** Type CH breakers
- **Voltage Rating:** 120/240V
- **Box Size:** 12

Supporting documents:

- [Eatons Volume 15-Solar Inverters and Electrical Balance of System](#)
- [Solar power centers](#)



- Eaton Specification Sheet -
CMBE4242PV200TS

Certifications:

- UL Listed

Product compliance:

- EUSERC Approved

© 2016 Eaton. All rights reserved.