



Powering Business Worldwide

pe.eaton.com

30.5 mm, Heavy-Duty Pushbutton Operator

10250T414

UPC:782113203737

Dimensions:

- **Height:** 2.1 IN
- **Length:** 3.4 IN
- **Width:** 2.4 IN

Weight: .3 LB

Warranties:

- 1 year

Specifications:

- **Type:** 30.5 mm, Heavy-Duty
- **Bezel:** Chrome
- **Illumination:** Illuminated
- **Led Lamp Number:** #755
- **Light Unit Type:** Incandescent, transformer
- **Light Unit Voltage:** 480 Vac
- **Mounting:** Flush
- **Operating Mode:** Momentary
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13
- **Series:** 10250T

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - 10250T414](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance:

- CE Marked



