



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Assembled Limit Switch

**E50ALR16PCY1**

**UPC:786685411132**

### Dimensions:

- **Height:** 2.46 IN
- **Length:** 4.62 IN
- **Width:** 1.54 IN

### Warranties:

- 1 year

### Specifications:

- **Type:** Assembly
- **Connection:** Mini
- **Contact Rating:** 10A at 240 Vac, 1A at 250 Vdc
- **Actuator:** Side rotary
- **Contact Configuration:** 1NO-1NC
- **Enclosure Material:** Die cast zinc
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67, IP69K
- **Led Indicators:** LED indicator
- **Light Unit Voltage:** 24-120 Vac/dc
- **Maximum Ac Current:** 10A
- **Maximum Dc Current:** 1A
- **Number Of Pins:** 5 pin
- **Operating Temperature:** 10° to 200°F
- **Series:** E50

### Supporting documents:

- [Eaton's Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50ALR16PCY1](#)

**Certifications:** No Data

**Product compliance:** No Data



