



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Non Plug-in Style Assembled Limit Switch

10316H296

UPC:782113229157

### Dimensions:

- **Height:** 7.34 IN
- **Length:** 1.55 IN
- **Width:** 1.78 IN

**Weight:**1.125 LB

**Notes:**Complete Assembled Switches; Consult factory for CE approval status

### Warranties:

- 1 year

### Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 10A at 600Vac, 0.22A at 125Vdc
- **Contact Configuration:** 1NO-1NC
- **Enclosure Material:** Die Cast Zinc
- **Environmental Rating:** NEMA 1, 4, 13
- **Maximum Ac Current:** 10A
- **Maximum Dc Current:** 0.22A
- **Operating Temperature:** -20° to 200°F (-29° to 93°C)
- **Switch Type:** Wobble Stick Nylon Rod

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - 10316H296](#)

### Certifications:

- UL Listed
- CSA Certified

### Product compliance:

- CE Marked



- Contact Manufacturer

---

© 2016 Eaton. All rights reserved.