



Powering Business Worldwide

pe.eaton.com

10316 Series, Type J Rotating Shaft Limit Switch

10316H77

UPC:782113228648

Dimensions:

- **Height:** 6.06 IN
- **Length:** 4.06 IN
- **Width:** 2.19 IN

Weight:3.5 LB

Warranties:

- 1 year

Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 10A at 600Vac, 10A at 240Vdc
- **Contact Configuration:** 1NO-1NC
- **Enclosure Material:** Die Cast Zinc
- **Environmental Rating:** NEMA 4
- **Maximum Ac Current:** 10A
- **Switch Type:** Rotating Shaft, Type J

Supporting documents:

- [Eaton Specification Sheet - 10316H77](#)

Certifications: No Data

Product compliance:

- Contact Manufacturer

