



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Continuous Duty AC Solenoid

10370H611

UPC:782113236360

### Dimensions:

- **Height:** 3.63 IN
- **Length:** 2.25 IN
- **Width:** 2.38 IN

**Notes:** Mounting of solenoids “with conduit box”—Size A are for wall mounting—Size B, C and D are for floor mounting.

### Warranties:

- 1 year

### Specifications:

- **Magnetic Force Against Gravity:** 0.55 lbs at 100% voltage, 0.33 lbs at 85% voltage
- **Magnetic Force Horizontal:** 0.72 lbs at 100% voltage, 0.50 lbs at 85% voltage
- **Magnetic Force With Gravity:** 0.90 lbs at 100% voltage, 0.68 lbs at 85% voltage
- **Frequency Rating:** 60 Hz
- **Full Load Current Range:** Inrush .92A/Sealed .17A
- **Mounting:** Wall mount
- **Operation:** Pull type
- **Size:** A
- **Special Features:** With conduit box
- **Voltage Rating:** 220A

### Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [Eaton Specification Sheet - 10370H611](#)

**Certifications:** No Data

**Product compliance:** No Data



