



Powering Business Worldwide

pe.eaton.com

LS-Titan Miniature DIN Limit Switch

LS-S11S-L

UPC:786685392820

Dimensions:

- **Height:** 3.78 IN
- **Length:** 1.22 IN
- **Width:** 1.32 IN

Weight: .1313 LB

Warranties:

- 1 year

Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 6A at 240Vac, 3A at 24Vdc
- **Contact Configuration:** 1NO-1NC, Snap Action, Positive Opening
- **Enclosure Material:** Polyamide PA66-GF25
- **Environmental Rating:** IP66, IP67
- **Maximum Ac Current:** 6A
- **Maximum Dc Current:** 3A
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Switch Type:** Long Roller Lever

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [LS-Titan Safety Limit Switches](#)
- [Eaton Specification Sheet - LS-S11S-L](#)

Certifications: No Data

Product compliance: No Data

