



Powering Business Worldwide

pe.eaton.com

Type BR Solar Power Center Loadcenters

BR4242PV200R

UPC:786685708270

Dimensions:

- **Height:** 45 IN
- **Length:** 5.19 IN
- **Width:** 14.31 IN

Weight:30 LB

Notes:Rainproof panels are furnished with hub closure plates. Type CSR main breaker factory installed.

Warranties:

- 10 year limited

Specifications:

- **Box Size:** L2R
- **Bus Material:** Copper
- **Bus Rating:** 225 A
- **Cover:** Cover included
- **Enclosure:** NEMA 3R
- **Input:** 70 max PV
- **Interrupt Rating:** 35 kAIC
- **Main Circuit Breaker:** 200A type CSR
- **Number Of Circuits:** 42

Supporting documents:

- [Eaton's Volume 15-Solar Inverters and Electrical Balance of System](#)
- [Solar power centers](#)
- [Eaton Specification Sheet - BR4242PV200R](#)

Certifications: No Data

Product compliance:

- NEC Compliant



