



Powering Business Worldwide

pe.eaton.com

Series C, K-frame Molded Case Circuit Breaker

HKD3250S10

UPC:786679077535

Dimensions:

- **Height:** 24 IN
- **Length:** 6 IN
- **Width:** 15 IN

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Amperage Rating:** 250A
- **Interrupt Rating:** 65 kAIC
- **Number Of Poles:** Three-pole
- **Voltage Rating:** 600V
- **Frame Size:** K-frame
- **Series:** Series C
- **Shunt Trip:** 110-240 Vac or 110-125 Vdc left pigtail rear
- **Trip Type:** Interchangeable thermal magnetic

Supporting documents:

- [310+ electronic trip units](#)
- [Eatons Volume 4-Circuit Protection](#)
- [K-Frame 310+ Molded-case circuit breakers](#)
- [Installation Instructions for DK, KDB, KD, HKD, KDC, KW, HKW, KWC, CKD, CHKD Circuit Breakers and Molded Case Switches](#)
- [Eaton Specification Sheet - HKD3250S10](#)
- [Instruction Leaflet for the KES 310+ Electronic Trip Unit](#)

Certifications:



- UL Listed

Product compliance: No Data

© 2016 Eaton. All rights reserved.