



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## S611 Soft Starter

**S611A077P3S**

**UPC:**786685480428

### Dimensions:

- **Height:** 19.45 IN
- **Length:** 7.64 IN
- **Width:** 11.58 IN

**Weight:**24 LB

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Circuit Breaker Type:** FDC
- **Fuse Size:** Class RK5/K5/J
- **Options:** Pump control
- **Amperage Rating:** 77A
- **Frame Size:** Frame A
- **Horsepower:** 60 hp
- **Mounting:** Vertical
- **Number Of Slots:** 2
- **Operating Temperature:** -20° to 50°C
- **Phase:** Three-phase
- **User Interface:** LCD
- **Voltage Rating:** 480V

### Supporting documents:

- [Eatons Volume 6-Solid-State Motor Control](#)
- [S611 Soft Starters](#)
- [S611 Soft Starter Quick Start Installation Guide](#)
- [S611 Frame A/B Soft Starter](#)
- [Eaton Specification Sheet - S611A077P3S](#)

### Certifications:

- UL Listed



- CSA file No. 3211-06
- IEC 60947-4-2

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.