



Powering Business Worldwide

pe.eaton.com

S611 Soft Starter

S611B099P3S

UPC:786685480435

Dimensions:

- **Height:** 19.45 IN
- **Length:** 7.46 IN
- **Width:** 11.58 IN

Weight:24 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Circuit Breaker Type:** FDC
- **Fuse Size:** Class RK5/K5/J
- **Options:** Pump control
- **Amperage Rating:** 99A
- **Frame Size:** Frame B
- **Frequency Rating:** 47-63 Hz
- **Full Load Current Range:** 48-99 FLA
- **Horsepower:** 75 hp
- **Mounting:** Vertical
- **Number Of Conductors:** 2
- **Operating Temperature:** -20° to 50°C
- **Operating Voltage:** 130-600V
- **Phase:** Three-phase
- **User Interface:** LCD
- **Voltage Rating:** 480V
- **Wire Size:** #14-2/0 AWG

Supporting documents:

- [Eatons Volume 6-Solid-State Motor Control](#)
- [S611 Soft Starters](#)
- [S611 Soft Starter Quick Start Installation Guide](#)



- [S611 Frame A/B Soft Starter](#)
- [Eaton Specification Sheet - S611B099P3S](#)

Certifications:

- IEC 60947-4-2
- UL Listed
- CSA file No. 3211-06

Product compliance: No Data

© 2016 Eaton. All rights reserved.