



Powering Business Worldwide

pe.eaton.com

Reduced Voltage Motor Starters-S611 Soft Starter

S611F414P3S

UPC:786685480503

Dimensions:

- **Height:** 9.5 IN
- **Length:** 29.69 IN
- **Width:** 17.56 IN

Weight:107 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Amperage Rating:** 414A
- **Frame Size:** F-frame
- **Max Hp Rating:** 150 hp at 208V, 150 hp at 240V, 350 hp at 480V, 450 hp at 600V
- **Phase:** Three-phase
- **Type:** Pump

Supporting documents:

- [Eatons Volume 6-Solid-State Motor Control](#)
- [S611 Soft Starters](#)
- [S611 Soft Starter Quick Start Installation Guide](#)
- [S611 Frame E/F Soft Starter](#)
- [Eaton Specification Sheet - S611F414P3S](#)

Certifications:

- IEC 60947-2
- CSA Std. C22.2 No.235
- UL 1077

Product compliance: No Data



