



Powering Business Worldwide

pe.eaton.com

E51 Series, Limit Switch Style, Modular Inductive Photoelectric Sensor

E51ALC1

UPC:782113213842

Dimensions:

- **Height:** 4.89 IN
- **Length:** 1.54 IN
- **Width:** 1.82 IN

Weight:.975 LB

Warranties:

- 3 year

Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 500 mA AC/DC Solid State Output
- **Contact Configuration:** NO or NC
- **Enclosure Material:** Receptacle and Body: Die Cast Zinc, Head: Plastic
- **Environmental Rating:** NEMA 3,3S,4,4X,6,6P,12,13, IP67
- **Input Voltage:** 20–264 Vac/dc
- **Led Indicators:** Green Power On, Amber Output Status
- **Maximum Ac Current:** 500 mA
- **Operating Mode:** Thru-Beam
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** Latching short circuit
- **Sensor Type:** Through Beam
- **Switch Type:** Photoelectric

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E51ALC1](#)



Certifications:

- UL Listed
- CSA Certified

Product compliance:

- CE Marked

© 2016 Eaton. All rights reserved.