



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## E57 Premium+ Series Short Body Tubular Inductive Proximity Sensor

E57SAL30T111

UPC:782113384795

### Dimensions:

- **Height:** 1.58 IN
- **Length:** 1.18 IN
- **Width:** 1.18 IN

**Weight:**.6063 LB

### Warranties:

- 1 year

### Specifications:

- **Accuracy:** < 1%
- **Connection:** 6.6 Ft. ( 2m ) Cable
- **Contact Rating:** 250 mA at 6-48Vdc
- **Cable Type:** PVC
- **Contact Configuration:** PNP Open Collector, Normally Open
- **Cord Length:** 79.2 FT
- **Diameter:** 1.18 IN
- **Enclosure Material:** Stainless Steel
- **Environmental Rating:** IP67, IP69K NEMA 4, 4X, 6, 6P
- **Input Voltage:** 6-48 Vdc
- **Led Indicators:** Red output status
- **Maximum Dc Current:** 500 mA
- **Operating Mode:** Shielded
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** Short circuit protected
- **Sensor Type:** Inductive Proximity

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)



- [Eaton Specification Sheet - E57SAL30T111](#)

**Certifications:** No Data

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.