



Powering Business Worldwide

pe.eaton.com

E47 Precision Limit Switch, Basic

E47BMS21

UPC:782113770840

Dimensions:

- **Height:** 2.41 IN
- **Length:** .69 IN
- **Width:** 1.19 IN

Weight:.0813 LB

Notes:Bottom facing M4 x 0.7 (8-32) terminal screws with cup washers will accept 22 -12 AWG (2.5 sq. mm maximum)

Warranties:

- 1 year

Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 15A at 125Vac / 15A at 14Vdc
- **Contact Configuration:** SPDT
- **Enclosure Material:** Mineral Filled Phenolic
- **Environmental Rating:** NEMA 1
- **Maximum Ac Current:** 15A
- **Operating Temperature:** -13° to 176°F (-25° to 80°C)
- **Switch Type:** Reversed Lever

Supporting documents:

- [E47 precision - Limit switches](#)
- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E47BMS21](#)

Certifications:

- CSA Certified
- UL Listed

Product compliance:

- CE Marked



