



Powering Business Worldwide

pe.eaton.com

60 Series Photoelectric Sensor Head

1161A-100

UPC:782113819518

Dimensions:

- **Height:** 3.5 IN
- **Length:** .75 IN
- **Width:** .75 IN

Weight:.4 LB

Warranties:

- 3 year

Specifications:

- **Cable Type:** PVC
- **Cord Length:** 108 FT
- **Diameter:** .75 IN
- **Enclosure Material:** Aluminum
- **Environmental Rating:** NEMA 3,4,6,12,13
- **Input Voltage:** 12 Vdc
- **Operating Mode:** Thu-Beam
- **Operating Temperature:** -40° to 158°F (-40° to 70°C)
- **Sensor Type:** Through Beam
- **Switch Type:** Photoelectric

Supporting documents:

- [Eaton Specification Sheet - 1161A-100](#)

Certifications: No Data

Product compliance:

- Contact Manufacturer

