



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## DOE 2016 Efficient Transformer, Dry-type, Ventilated, Three- phase

**V24M28T3016**

**UPC:**786680175183

### Dimensions:

- **Height:** 43 IN
- **Length:** 28 IN
- **Width:** 32 IN

**Weight:**402 LB

**Notes:**10 CFR Part 431 (2016) Efficient

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Coil Material:** Aluminum
- **Efficiency:** DOE2016
- **Enclosure:** NEMA 2
- **Frame:** 940
- **Frequency Rating:** 60 Hz
- **Insulation:** 220C
- **Kva Rating:** 30 kVA
- **Material:** Al windings
- **Phase:** Three-phase
- **Primary Voltage:** 240V Delta
- **Secondary Voltage:** 208Y/120V
- **Sound Level:** NEMA ST-20
- **Tap Size:** +2,-4 at 2.5%
- **Temperature Rating:** 150°C rise
- **Weathershield:** WS58
- **Wiring Connection:** 280C

**Supporting documents:**



- [Eaton Specification Sheet - V24M28T3016](#)

**Certifications:** No Data

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.