



Powering Business Worldwide

pe.eaton.com

## General Purpose Power Supply

**PSG240E24RM**

**UPC:**786685683553

### Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

**Warranties:** No Data

### Specifications:

- **Operating Temperature:** -20° to 75°C
- **Wattage:** 240W
- **Degree Of Protection:** IP20
- **Enclosure Material:** Aluminum
- **Frequency Rating:** 47-63 Hz
- **Input Voltage:** 100-240 Vac
- **Mounting:** DIN rail mount
- **Nominal Voltage:** 24 Vdc ( $\pm 4.8$  Vdc)
- **Output:** 24 Vdc/2.5A
- **Phase:** Single-Phase

### Supporting documents:

- [Eatons PSG Series Power Supplies](#)
- [Installation Instructions for PSG240E Power Supply](#)
- [PSG240E24RM 2D Drawing Xchange](#)
- [Eaton Specification Sheet - PSG240E24RM](#)
- [PSG240E24RM AutoCAD 2D Footprint \(mm\)](#)
- [PSG240E24RM AutoCAD 2D Footprint](#)
- [PSG240E24RM 3D Inventor](#)
- [PSG240E24RM 2D PDF](#)
- [PSG240E24RM 3D Model Xchange](#)

### Certifications:

- cULus/UL 60950-1
- SELV (EN 60950)
- EN 61000-4-11



- EN 60204
- EN 50178
- EN 61000-4-2
- IEC Rated
- UL 508
- PELV (EN 60204)
- EN 61000-406
- CSA Certified
- EN 61000-6-3
- EN 61000-6-2
- EN 610003-2

**Product compliance:**

- German Safety
- DIN 57100-410
- CE Marked
- RoHS Compliant