



Powering Business Worldwide

pe.eaton.com

Special Purpose Limit Switch

E50GG1

UPC:782113304090

Dimensions:

- **Height:** 2.46 IN
- **Length:** 4.22 IN
- **Width:** 1.54 IN

Weight: .5 LB

Warranties:

- 1 year

Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 5A at 250V
- **Contact Configuration:** 1NO-1NC
- **Enclosure Material:** Die cast zinc
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67
- **Maximum Ac Current:** 5A
- **Operating Temperature:** 14° to 201°F (-10° to 94°C)
- **Series:** E50
- **Switch Type:** Gravity return

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50GG1](#)

Certifications:

- CSA Certified
- UL Listed

Product compliance: No Data

