



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)



## Premium+ Inductive Proximity Sensor

**E57LBL12A2SA**

**UPC:**782113604817

### Dimensions:

- **Height:** .47 IN
- **Length:** 2.69 IN
- **Width:** .47 IN

### Warranties:

- 1 year

### Specifications:

- **Type:** Premium+ Inductive Proximity Sensor
- **Accuracy:** <3% sensing range
- **Connection:** Dual key micro
- **Contact Rating:** 250 mA at 250V
- **Contact Configuration:** 2-wire AC, NC
- **Diameter:** .472440948 MM
- **Enclosure Material:** 303 stainless steel
- **Environmental Rating:** NEMA 4, 4X, 6, 6P, 12, 13, IP67, IP69K
- **Input Voltage:** 20-250V
- **Led Indicators:** 360° viewable LED
- **Maximum Ac Current:** 250 mA
- **Number Of Pins:** 3 pin
- **Operating Mode:** Shielded
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Series:** E57

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E57LBL12A2SA](#)

### Certifications:

- CSA Certified
- UL Listed

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.