



Powering Business Worldwide

pe.eaton.com

CE Marked Control Transformer

CE0250K2VCEFS

UPC:786680041570

Dimensions:

- **Height:** 3.858 IN
- **Length:** 5.512 IN
- **Width:** 4.488 IN

Weight:14.9 LB

Notes:Epoxy resin impregnated coil design, 50/60 Hz operation, 180°C insulation system

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Coil Material:** Copper windings
- **Design:** MTK
- **Modification 1:** Factory-mounted finger-safe terminal shields
- **Primary Voltage:** 208/230/400/460/575V
- **Secondary Voltage:** 24/115/230V
- **Tap Size:** None
- **Temperature Rating:** 115°C
- **Type:** CE Marked Control Transformer
- **Volt Ampere Rating:** 250 VA

Supporting documents:

- [Eaton's Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - CE0250K2VCEFS](#)

Certifications:

- UL Listed
- CSA Certified
- IEC 61558-2



- cUL Certified

Product compliance:

- RoHS Compliant

© 2016 Eaton. All rights reserved.