



Powering Business Worldwide

pe.eaton.com

Premium+ Inductive Proximity Sensor

E57LAL30T110

UPC:782113743080

Dimensions:

- **Height:** 1.18 IN
- **Length:** 3.39 IN
- **Width:** 1.18 IN

Warranties:

- 1 year

Specifications:

- **Type:** Premium+ Inductive Proximity Sensor
- **Accuracy:** <3% sensing range
- **Contact Rating:** 500 mA at 6-30 Vdc
- **Cable Type:** PVC
- **Contact Configuration:** NO NPN open collector
- **Cord Length:** 79.2 FT
- **Diameter:** 1.18110237 MM
- **Enclosure Material:** 303 stainless steel
- **Environmental Rating:** NEMA 4, 4X, 6, 6P, 12, 13, IP67, IP69K
- **Input Voltage:** 6-48 Vdc
- **Led Indicators:** 360° viewable LED
- **Maximum Dc Current:** 500 mA
- **Operating Mode:** Shielded
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** Auto reset
- **Series:** E57

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E57LAL30T110](#)

Certifications:



- UL Listed
- CSA Certified

Product compliance: No Data

© 2016 Eaton. All rights reserved.