



Powering Business Worldwide

pe.eaton.com

E10 Series Light Industrial Toggle Switch

E10T215AS

UPC:782113698236

Dimensions:

- **Height:** 2.1 IN
- **Length:** .8 IN
- **Width:** .7 IN

Weight:.07 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Toggle Switch
- **Bushing Length:** 0.47 inch bushing
- **Lever Length:** 0.563 inch lever
- **Number Of Poles:** Two-pole
- **Number Of Positions:** ON, None, OFF
- **Rating:** 15A at 125 Vac, 10A at 250 Vac, 3/4 hp at 50 Vac
- **Series:** E10
- **Terminals:** Screw
- **Throw Type:** Single-throw

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - E10T215AS](#)

Certifications:

- UL Recognized
- CSA Certified

Product compliance: No Data



