



Powering Business Worldwide

pe.eaton.com

Mini-Power Center

P48G11S03SS

UPC:786680023828

Dimensions:

- **Height:** 27.5 IN
- **Length:** 8.9 IN
- **Width:** 11.9 IN

Weight:139 LB

Notes:Grade 304 stainless steel enclosure

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Mini-power center
- **Coil Material:** Aluminum windings
- **Enclosure:** NEMA 3RX
- **Frame:** 283
- **Frequency Rating:** 60 Hz
- **Phase:** Single-phase
- **Primary Voltage:** 480V
- **Secondary Voltage:** 120/240V
- **Tap Size:** 2 at -5% FCBN
- **Temperature Rating:** 115°C
- **Volt Ampere Rating:** 3 KVA
- **Weathershield:** Indoor-Outdoor
- **Wiring Connection:** 97A3K

Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - P48G11S03SS](#)

Certifications:

- CSA Certified
- IEEE Certified



- ANSI
- UL Listed

Product compliance:

- NEMA Compliant

© 2016 Eaton. All rights reserved.