



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Inductive Proximity Pancake Sensor

**E56CAL70B1S1**

**UPC:**782113378978

### Dimensions:

- **Height:** 1.63 IN
- **Length:** 5.29 IN
- **Width:** 4.35 IN

### Warranties:

- 1 year

### Specifications:

- **Type:** Inductive Proximity Pancake Sensor
- **Accuracy:** <3%
- **Connection:** Mini
- **Contact Rating:** 400 mA at 250V
- **Contact Configuration:** 2-wire AC, NO
- **Enclosure Material:** PPS housing, aluminum baseplate
- **Environmental Rating:** NEMA 4, 4X, 6, 6P, 12, 13, IP67
- **Input Voltage:** 90-260V 45/65 Hz
- **Led Indicators:** Output status
- **Maximum Ac Current:** 400 mA
- **Number Of Pins:** 3 pin
- **Operating Mode:** Unshielded
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** S/C with auto-reset
- **Series:** E56

### Supporting documents:

- [E52Q Cube and E56 Pancake inductive sensors](#)
- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E56CAL70B1S1](#)



**Certifications:** No Data

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.