



Powering Business Worldwide

pe.eaton.com

RS Series Safety Interlock Switch

RS2R-02-C3

UPC:786685884837

Dimensions:

- **Height:** 2 IN
- **Length:** .94 IN
- **Width:** .44 IN

Weight: .3625 LB

Notes:0

Warranties:

- 1 year

Specifications:

- **Type:** LIMIT SWITCHES
- **Accuracy:** < 10%
- **Connection:** 10 Ft. (3m) Cable
- **Contact Rating:** 300 mA at 24 Vdc
- **Cable Type:** PVC
- **Contact Configuration:** 2 Normally Closed Contacts
- **Cord Length:** 120 FT
- **Enclosure Material:** Polyamide
- **Environmental Rating:** IP67, IP69K
- **Maximum Dc Current:** 300 mA
- **Operating Temperature:** 14° to 131°F (-10° to 55°C)
- **Switch Type:** Magnetic Reed Switch

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - RS2R-02-C3](#)

Certifications: No Data

Product compliance: No Data



