



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Quicklag Industrial Ground Fault Thermal-Magnetic Circuit Breaker

**QCGFT1015T**

**UPC:**786679139875

### Dimensions:

- **Height:** 1.2 IN
- **Length:** 5.1 IN
- **Width:** 3.3 IN

**Weight:**.4 LB

**Notes:**HACR rated

### Warranties:

- 1 year

### Specifications:

- **Type:** Quicklag
- **Special Features:** 5 mA Trip Sensitivity
- **Amperage Rating:** 15A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Single-pole
- **Voltage Rating:** 120/240V
- **Circuit Breaker Type:** QCGF
- **Trip Type:** Non-Interchangeable
- **Mounting:** Bolt-on

### Supporting documents:

- [Eaton Specification Sheet - QCGFT1015T](#)

**Certifications:** No Data

**Product compliance:** No Data

