



Powering Business Worldwide

pe.eaton.com

DOE 2016 Efficient Transformer, Dry-type, Ventilated, Three- phase

V48M47T3316

UPC:786680175251

Dimensions:

- **Height:** 66.18 IN
- **Length:** 33.5 IN
- **Width:** 42.18 IN

Weight:1.1 LB

Notes:10 CFR Part 431 (2016) Efficient

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Coil Material:** Aluminum
- **Efficiency:** DOE2016
- **Enclosure:** NEMA 2
- **Frame:** 945
- **Frequency Rating:** 60 Hz
- **Insulation:** 220C
- **Kva Rating:** 300 kVA
- **Phase:** Three-phase
- **Primary Voltage:** 480 DELTA
- **Secondary Voltage:** 480Y/277
- **Sound Level:** NEMA ST-20
- **Tap Size:** 2 at +2.5%, 4 at -2.5%
- **Temperature Rating:** 150°C rise
- **Weathershield:** WS62
- **Wiring Connection:** 280B

Supporting documents:

- [Eaton Specification Sheet - V48M47T3316](#)



Certifications: No Data

Product compliance: No Data

© 2016 Eaton. All rights reserved.