



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## FERRUPS UPS

FI300AA0A0A0A0B

UPC:743172067128

### Dimensions:

- **Height:** 29.5 IN
- **Length:** 25 IN
- **Width:** 15.5 IN

**Weight:**348 LB

### Warranties:

- 2 year

### Specifications:

- **Special Features:** AVR/ DVR (recommended for PFC loads)
- **Battery Type:** Standard battery, standard charger
- **Efficiency:** 90% efficiency
- **Humidity:** 5 to 95% non-condensing
- **Input:** Hardwired, Input Isolation Transformer
- **Operating Temperature:** 0° to 40°C
- **Output:** Hardwired
- **Output Voltage:** 120/240V
- **Phase:** Single-phase
- **Topology:** Ferroresonant
- **User Interface:** On/off switch, alarm switch, 5 front indicator lights
- **Volt Ampere Rating:** 4300 KVA

### Supporting documents:

- [Eaton FERRUPS UPS](#)
- [Product and Service Catalog](#)
- [Eaton Specification Sheet - FI300AA0A0A0A0B](#)

### Certifications:

- FCC Cat. A
- IEC 801-4
- IEC 801-2



- UL Listed
- ANSI/IEEE Std C62.45
- IEC 801-5
- ANSI/IEEE Std C62.41
- CSA Certified

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.