



Powering Business Worldwide

pe.eaton.com

Quicklag Industrial Ground Fault Thermal-Magnetic Circuit Br

QBGFT2025

UPC:786676026727

Dimensions:

- **Height:** 2 IN
- **Length:** 4.5 IN
- **Width:** 2.75 IN

Weight:.6 LB

Notes:HACR rated

Warranties:

- 1 year

Specifications:

- **Type:** Ground fault self test
- **Special Features:** 5 mA Trip Sensitivity
- **Amperage Rating:** 25A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Single-pole
- **Voltage Rating:** 120/240V
- **Circuit Breaker Type:** QB
- **Trip Type:** Non-Interchangeable
- **Mounting:** Bolt-on

Supporting documents:

- [Eaton Specification Sheet - QBGFT2025](#)

Certifications: No Data

Product compliance: No Data

