



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## General-Purpose Encapsulated Transformer

**S20N11P02S64X**

**UPC:**786680116346

### Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

**Notes:**NEMA 4X Grade 316 stainless steel enclosure.

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** General-purpose encapsulated transformer
- **Design:** EP
- **Coil Material:** Copper windings
- **Enclosure:** NEMA 4X
- **Frame:** 68P4X
- **Frequency Rating:** 60 Hz
- **Phase:** Single-phase
- **Primary Voltage:** 240 x 480V
- **Secondary Voltage:** 120/240V
- **Tap Size:** None
- **Temperature Rating:** 115°C
- **Volt Ampere Rating:** 2 KVA
- **Weathershield:** Indoor-Outdoor

### Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - S20N11P02S64X](#)

**Certifications:** No Data



**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.