



Powering Business Worldwide

pe.eaton.com

Heavy-Duty Hesitation Switch- One Hole Panel Mount

7990K12

UPC:782116571314

Dimensions:

- **Height:** .97 IN
- **Length:** 1.45 IN
- **Width:** 1.32 IN

Notes:Listed rating for 125 Vac also applies at 28 Vdc

Warranties:

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warranted for one (1) year from the date of shipment.

Specifications:

- **Type:** Bat lever
- **Amperage Rating:** 15A at 125 Vac, 10A at 250 Vac
- **Bushing Length:** 0.468-inch
- **Circuit Number:** F
- **Circuit Position Center:** OFF
- **Circuit Position Down:** ON
- **Horsepower:** 0.75 hp at 250 Vac
- **Lever Length:** 0.687-inch
- **Number Of Poles:** Four-pole
- **Terminals:** 0.250-inch spade terminal
- **Throw Type:** Double-throw

Supporting documents:

- [Eatons Volume 11-Vehicle and Commercial Controls](#)
- [Eaton Specification Sheet - 7990K12](#)

Certifications:



- UL Recognized

Product compliance: No Data

© 2016 Eaton. All rights reserved.