



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## 60A 600V, 3P 3W, NF N12 w/ Viewing Window, Painted Orange

**DH362UDKW-ORNG**

**UPC:**786679160671

### Dimensions:

- **Height:** 10.5 IN
- **Length:** 23 IN
- **Width:** 12.5 IN

**Weight:**22 LB

**Notes:**For 2-pole applications; use outside poles of 3-pole switch. Can be field modified to meet NEMA 3R rainproof requirements when a factory provided drain hole is opened.

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Special Features:** Upper viewing window
- **Type:** Single-Throw
- **Amperage Rating:** 60A
- **Enclosure:** NEMA 12
- **Enclosure Material:** Painted galvanized steel
- **Fuse Configuration:** Non-fusible
- **Number Of Poles:** Three-pole
- **Number Of Wires:** Three-wire
- **Product Category:** Heavy Duty, Non-Fusible
- **Voltage Rating:** 600V
- **Max Hp Rating:** 10 at 240 Vac TD 1 Ph, 20 at 480 Vac TD 1 Ph, 25 at 600 Vac TD 1 Ph, 20 at 240 Vac TD 3 Ph, 50 at 480 Vac TD 3 Ph, 60 at 600 Vac TD 3 Ph, 10 at 250 Vdc



**Supporting documents:**

- [Eaton Specification Sheet - DH362UDKW-ORNG](#)

**Certifications:**

- UL Listed

**Product compliance:** No Data